
6400/6500

PRIVACY HOSPITAL PUSH/PULL LATCH



Patent No. 6,196,599
6,293,598

**WHEN ORDERING,
Please list:**

Backset

Strike


Finish

**Engraving
(if required)
Add Suffix P
Indicate how handles
are mounted**

- Privacy thumbturn lock on one side, emergency unlock on opposite side.
- 6400 Pull side lock. 6500 Push side lock.
- Available with 2-3/4", 5" or 7" backset.
- Standard or ASA strike.
- All standard finishes.
- Meets ADA requirements.
- Standard for 1-3/4" doors.
- UL listed.

6400 PRIVACY LATCH - PULL SIDE LOCK

UL US LISTED



NOTE:
BEFORE MOUNTING PUSH AND PULL HANDLES,
CAM PIN MUST BE ROTATED TOWARD SIDE
INDICATED BY ARROW STAMPED ON BASE

ITEM	QTY	PART	ITEM	QTY	PART
1	4	10-32 KEPNUT	14	1	PUSH SIDE HANDLE
2	4	10-32x2-3/4" PH. PAN HD. M.S.	15	1	CAM ASSEMBLY (FEMALE)
3	2	FORK	16	1	PRIVACY LOCK KNOB
4	2EA	WASHERS & C-RING	17	1	LOCKING CAM ASSEMBLY
5	2	SPRING	18	1	LOCKING SHAFT
6	2	MOUNTING BRACKET	19	2	10-32X1/4LG., B.H.S.C.S.
7	4EA	HANDLE SHAFT & COTTER PIN	20	2	1/4-20X3/8LG. B.H.S.C.S.
8	1	PULL SIDE HANDLE	21	2	FLAT WASHER
9	1	CAM ASSEMBLY (MALE)	22	2	BOWED RETAINER RING
10	1	OVER RIDE KNOB	23	1	LABEL "ARROW"
11	1	OVER RIDE CAM ASSEMBLY	24	2	WAVE WASHER
12	1	COVER (OVER-RIDE)	25	1	COVER (LOCKING)
13	4	8-32 X 3/8" F.H.M.S.			

NOTES:

1. PREP DOOR PER 6000 TEMPLATE.
2. OVER-RIDE CAM (ITEM 11) & LOCKING SHAFT (ITEM 18) PROVIDED ASSEMBLED ON PULL SIDE HANDLE ASSEMBLY.
3. MOUNT PULL SIDE HANDLE ON DOOR (ITEM 8).
4. INSTALL PUSH SIDE HANDLE TO DOOR USING ITEM 1 & 2. SLIDE WAVE WASHER (ITEM 11) OVER LOCKING SHAFT (ITEM 18) AND SECURE WITH 10-32 X 3/8" PAN HD SCREW W/STAR WASHER (ITEM 19).
5. INSTALL LOCKING COVER (ITEM 25) ON PULL SIDE WITH (2) 8-32 X 3/8 FHMS SCREWS (ITEM 13).
6. INSTALL OVER-RIDE COVER (ITEM 12) ON PUSH SIDE WITH (2) 8-32 X 3/8 FHMS SCREWS (ITEM 13).
7. AFFIX "ARROW" LABEL (ITEM 23) TO LEFT OF LOCK LEVER (ITEM 16) AS SHOWN ABOVE.

PATENT No. 6,196,599 & 6,293,598

